

Water Technologies & Solutions fact sheet

AG HR series

high rejection brackish water RO elements

The A-Series family of proprietary thin-film reverse osmosis membrane is characterized by high flux and high sodium chloride rejection. AG HR brackish water elements are selected when high rejection and operating pressures as low as 200 psi (1,379 kPa) are desired. These elements are recommended for brackish water with salt concentration (TDS) levels between 1,000 and 10,000mg/l or when very high salt rejection of monovalent ions is required.

AG HR series is certified to NSF/ANSI 61.

Table 1: Element Specification

Membrane	A-series, thin-film membrane (TFM*)				
Model	Average permeate flow gpd (m²/day) (1)(2)	Average NaCl rejection (1)(2)	Minimum NaCl re- jection (1)(2)		
AG-90	2400 (9.1)	99.8%	99.3%		
AG-365	10,000 (37.9)	99.8%	99.3%		
AG-400	11,000 (41.6)	99.8%	99.3%		
AG-400 FR,34	11,000 (41.6)	99.8%	99.3%		
AG-440	12,000 (45.4)	99.8%	99.3%		

(1) Average salt rejection after 24 hours operation. Individual flow rate may vary ±20%.

(2) Testing conditions: 2,000ppm NaCl solution at 225psi (1,550kPa) operating pressure, 77°F (25°C), pH7 and 15% recovery.

Model	Active area ft² (m²)	Outer wrap	Part number
AG-90	90 (8.4)	Fiberglass	3056665
AG-365	365 (33.9)	Fiberglass	3056666
AG-400	400 (37.2)	Fiberglass	3056667
AG-400 FR,34	400 (37.2)	Fiberglass	3056668
AG-440	440 (40.9)	Fiberglass	3056669




Figure 1a: Element Dimensions Diagram – Female






Table 2: Operating and CIP parameters

Typical Operating Pres- sure	200 psi (1,380 kPa)	
Typical Operating Flux	10-20GFD (15-35LMH)	
Maximum Operating Pressure	600 psi (4,137 kPa)	
Maximum Temperature	Continuous operation: 122°F (50°C) Clean-In-Place (CIP): 122°F (50°C)	
pH range	Optimum rejection: 7.0-7.5, Continuous operation 2.0 – 11.0 Clean-In-Place (CIP): 1.0-13.0 (1)	
Maximum Pressure Drop	Over an element: 15 psi (103 kPa) Per housing: 50 psi (345 kPa)	
Chlorine Tolerance	1,000+ ppm-hours, dechlorination recommended	
Feedwater	NTU < 1 SDI ₁₅ < 5	

(1) Refer to Cleaning Guidelines Technical Bulletin TB1194

Find a contact near you by visiting <u>www.suezwatertechnologies.com</u> and clicking on "Contact Us." *Trademark of SUEZ; may be registered in one or more countries. ©2019 SUEZ. All rights reserved.

Table 3: Dimensions and Weights

	Туре	Dimensions, inches (cm)			Boxed
Model		Α	В	С	Weight lbs (kg)
AG-90	Male	40.0 (101.6)	0.75 (1.90)	3.9 (9.9)	9 (4)
AG-365	Female	40.0 (101.6)	1.125 (2.86)	7.9 (20.1)	35 (16)
AG-400	Female	40.0 (101.6)	1.125 (2.86)	7.9 (20.1)	35 (16)
AG-400 FR,34	Female	40.0 (101.6)	1.125 (2.86)	7.9 (20.1)	35 (16)
AG-440	Female	40.0 (101.6)	1.125 (2.86)	7.9 (20.1)	35 (16)